

Material Safety Data Sheet

Panduit
17301 Ridgeland Ave.
Tinley Park, IL 60477
Phone: 708-532-1800
Fax: 708-532-1811

PRODUCT NAME: Acrylic Pressure Sensitive Adhesive Foam
Mounting Tape with Paper Liner

PART NUMBER: P32W2A2
AAP2-250
T111P
MSDS NUMBER: 4007

CHEMICAL FAMILY: N/A

*****SECTION II – HAZARDOUS INGREDIENTS*****

HAZARDOUS INGREDIENTS	CAS#	WT%	TLV
-----------------------	------	-----	-----

None known

Hazardous Mixtures of Other Liquids, Solids or Gases: None known

* Subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 and of 40 CFR 372. This information must be included in all MSDS's that are copied and distributed for this material.

*****SECTION III – PHYSICAL DATA *****

<u>Boiling Point (F):</u>	N/A	<u>Specific Gravity (H₂O=1):</u>	Lighter than water
<u>Vapor Pressure (mm Hg.):</u>	N/A	<u>Volatile by Volume (%):</u>	<0.5
<u>Vapor Density (AIR=1):</u>	N/A	<u>Evaporation Rate (Butyl Acetate=1):</u>	N/A

Solubility In Water: >2%

Appearance and Odor: White in color, no particular odor.

*****SECTION IV – FIRE AND EXPLOSION HAZARD DATA*****

Flash Point (On Conc.): >350°F (various methods)

Flammable Limits: LEL-N/A UEL-N/A

Extinguishing Media: Water, CO₂, Dry Chemical or Waterfog.

Special Fire Fighting Procedures: Nothing special – do not enter confined fire space without proper protective equipment including NIOSH approved self-contained, breathing apparatus.

Unusual Fire and Explosion Hazards: None known

*****SECTION V – HEALTH HAZARD DATA*****

First Aid Procedures:

Inhalation - Remove to fresh air; if not breathing, give artificial respiration, preferably mouth-to-mouth; if breathing is difficult, give oxygen, call physician.

Eye- See physician

Skin- No known effect

THIS PRODUCT IS NOT A KNOWN CARCINOGENIC, TERATONGENIC OR MUTANT

Effects of Overexposure: Inhalation: not likely; burning material may give off fumes which may cause nose and throat irritation, headache and nausea. Skin contact: no known effect. Indigestion: not likely.

*****SECTION VI – REACTIVITY DATA*****

Stability: Stable Conditions to Avoid: N/A
Incompatibility (Materials to Avoid): None known

Hazardous Decomposition Products: Carbon monoxide, Carbon dioxide

Hazardous Polymerization: Will not occur Conditions to Avoid: N/A

*****SECTION VII – SPILL OR LEAK PROCEDURES*****

Steps to be Taken in Case Material is Released or Spilled: Place in suitable receptacle.

Waste Disposal Method: Land fill in accordance with applicable federal, state and local law or regulation.

*****SECTION VIII – SPECIAL PROTECTION INFORMATION*****

Respiratory Protection: Not necessary

Ventilation: Local Exhaust:
Mechanical (General):
Special:
Other: Nothing special required

Protective Gloves: Not normally needed
Eye Protection: Not normally needed
Other Protective Equipment: Not normally needed

*****SECTION IX – SPECIAL PRECAUTIONS*****

Precautions to be Taken in Handling and Storing: Keep away from sources of ignition.

Other Precautions: Consult your occupational safety and health specialist to insure that suggested handling procedures will be adequate and in compliance with applicable laws and regulations.

*****NFPA HAZARDOUS IDENTIFICATION*****

Health - Fire - Reactivity –

*****LIABILITY DISCLAIMER*****

The information in this MSDS was obtained from sources which we believe are reliable. HOWEVER, THE INFORMATION IS PROVIDED WITHOUT ANY WARRANTY, EXPRESSED OR IMPLIED, REGARDING ITS CORRECTNESS.

The conditions or methods of handling, storage, use and disposal of the product are beyond our control and may be beyond our knowledge. FOR THIS AND OTHER REASONS, WE DO NOT ASSUME RESPONSIBILITY AND EXPRESSLY DISCLAIM LIABILITY FOR LOSS, DAMAGE OR EXPENSE ARISING OUT OF, OR IN ANY WAY CONNECTED WITH THE HANDLING, STORAGE, USE OR DISPOSAL OF THE PRODUCT.

For additional information, contact: PANDUIT CORP. Global Safety & Security Manager @ 708-532-1800

Previous Revision Date: 04/17/01
Last Revision Date: 11/07/07

FOR EMERGENCY INFORMATION CALL:
1-800-535-5053 (US)
1-352-323-3500 (International)
24 HOURS A DAY – 7 DAYS A WEEK